

## CERTIFICATE OF ANALYSIS

Thermo Fisher Scientific's Quality System has been found to conform to Quality Management System Standard ISO9001:2015 by TUV SUD America Inc.  
 Certificate Number. 951001163

Catalogue Number	033262
Lot Number	R27M025
Description	Oxalic acid dihydrate, ACS, 99.5-102.5%
CAS Number	6153-56-6
Quality Test/Release Date	28/May/2026
Suggested retest date	28/May/2031
Country of Origin	India
Declaration of Origin	Synthetic
BSE/TSE	Not directly derived from or manufactured with any animal byproducts in any way (including but not limited to fermentation or nutrient broth, catalysts, enzymes).

Result Name	Units	Specifications	Test Value
Assay (Redox Titration)	%	99.5-102.5%	99.87
Calcium content	%	≤0.001%	0.0001
Chloride content	%	≤0.002%	<0.002
Appearance (Color)		White or colorless	Colorless
Iron content	ppm	≤2ppm	<2
Form		Crystalline powder or solid	Solid
Residue on ignition	%	≤0.01%	0.0085
Insoluble material	%	≤0.005%	0.003
Nitrogen compounds (as N)	%	≤0.001%	<0.001
Heavy Metals (as Pb)	ppm	≤5ppm	<5
Substances Darkened by H2SO4		Passes test	Passes test
Sulfate content	%	≤0.005%	<0.005



Derek Roy  
 Quality Manager, LCD

Products are processed under ISO 9001:2015 quality management systems and samples are tested for conformance to the noted specifications. Certain data may have been supplied by third parties. We disclaim the implied warranties of merchantability and fitness for a particular purpose, and the accuracy of third-party data or information associated with the product. Products are for research and development use only. Products are not for direct administration to humans or animals. It is the responsibility of the final formulator or end user to determine suitability, and to qualify and/or validate each product for its intended use.

Note: The data listed is valid for all package sizes of this lot of this product, expressed as an extension of the catalogue number listed above.