

CERTIFICATE OF ANALYSIS

Thermo Fisher Scientific's Quality System has been found to conform to Quality Management System Standard ISO9001:2015 by TUV SUD America Inc.
 Certificate Number. 951001163

Catalogue Number	022921
Lot Number	T30L728
Description	Chlorobenzene, Spectrophotometric Grade, 99.9%
CAS Number	108-90-7
Quality Test/Release Date	19/Aug/2025
Suggested retest date	19/Aug/2028
Country of Origin	India
Declaration of Origin	Synthetic
BSE/TSE	Not directly derived from or manufactured with any animal byproducts in any way (including but not limited to fermentation or nutrient broth, catalysts, enzymes).

Result Name	Units	Specifications	Test Value
Assay (GC)	%	≥99.9% (excluding water) =/-US UK]	99.99
Appearance (Color)		Clear colorless	Clear colorless
Form		Liquid	Liquid
Water Content (Karl Fischer Titration)	%	≤0.03% (300ppm) =/-US] / ≤0.01% (100ppm) =/-UK]	0.01
Optical Absorbance at	AU	400nm: ≤0.005AU	<0.001
Optical Absorbance at	AU	350nm: ≤0.02AU =/-US]	0.01
Optical Absorbance at	AU	325nm: <0.04AU =/-US]	0.03
Optical Absorbance at	AU	300nm: ≤0.05AU =/-US]	0.04
Optical Absorbance at	AU	288nm: ≤1.00AU =/-US]	0.65
Residue on Evaporation	ppm	≤2ppm (0.0002%) =/-US] / ≤0.0001% (1ppm) =/-UK]	2



Luis Perez
 Interim Director Quality, LCD

Products are processed under ISO 9001:2015 quality management systems and samples are tested for conformance to the noted specifications. Certain data may have been supplied by third parties. We disclaim the implied warranties of merchantability and fitness for a particular purpose, and the accuracy of third-party data or information associated with the product. Products are for research and development use only. Products are not for direct administration to humans or animals. It is the responsibility of the final formulator or end user to determine suitability, and to qualify and/or validate each product for its intended use.

Note: The data listed is valid for all package sizes of this lot of this product, expressed as an extension of the catalogue number listed above.