

CERTIFICATE OF ANALYSIS

Thermo Fisher Scientific's Quality System has been found to conform to Quality Management System Standard ISO9001:2015 by Intertek. Certificate Number. 2317548

Catalogue Number	22674
Lot Number	A0442997
Description	Thymidine,99+%
CAS Number	50-89-5
Quality Test/Release Date	08/Dec/2024
Suggested retest date	08/Dec/2029
Country of Origin	CHINA
Declaration of Origin	other
BSE/TSE	made by fermentation with D-Glucose from plant origin

Result Name	Units	Specifications	Test Value
Appearance (Color)		White to almost white	White
Appearance (Form)		Crystalline powder	Crystalline powder
Infrared spectrum		Conforms	Conforms
UV spectrophotometry	%	98.0 to 102.0 (lambda max. 267 nm, pH 7)	99.5 (lambda max. 267 nm, pH 7)
UV spectrophotometry		molar absorptivity 9600 +/- 4%, on dry basis	molar absorptivity 9600 +/- 4%, on dry basis
HPLC	%	>=99.0	99.9
Water	%	=<0.5 (K.F.)	0.4 (K.F.)
Heavy metals (as Pb)	ppm	=<10	=<10
Sulfated ash	%	=<0.3 (800°C)	=<0.3 (800°C)
Specific optical rotation	nm	+17.5° to +19.5° (20°C, 589 (c=3, H2O)	+17.8° (20°C, 589) (c=3, H2O)
Ratio of Absorbances		0.62 to 0.68 (A250/A260)	0.64 (A250/A260)
Ratio of Absorbances		0.70 to 0.76 (A280/A260)	0.71 (A280/A260)



Geert Torfs
Supervisor, QC

Products are processed under ISO 9001:2015 quality management systems and samples are tested for conformance to the noted specifications. Certain data may have been supplied by third parties. We disclaim the implied warranties of merchantability and fitness for a particular purpose, and the accuracy of third-party data or information associated with the product. Products are for research and development use only. Products are not for direct administration to humans or animals. It is the responsibility of the final formulator or end user to determine suitability, and to qualify and/or validate each product for its intended use.

Note: The data listed is valid for all package sizes of this lot of this product, expressed as an extension of the catalogue number listed above.