

**CERTIFICATE OF ANALYSIS**

Thermo Fisher Scientific's Quality System has been found to conform to Quality Management System Standard ISO9001:2015 by INTERTEK SAI Global Certificate Number. QMS42099

Catalogue Number	P/7507
Lot Number	2560530
Description	Propan-2-ol HPLC Solvent HPLC
CAS Number	67-63-0
Quality Test/Release Date	18/Nov/2025
Expiry Phrase	Use within 5 years of opening
Country of Origin	Netherlands
Declaration of Origin	Synthetic
BSE/TSE	Not directly derived from or manufactured with any animal byproducts in any way (Including but not limited to fermentation or nutrient broth, catalysts, enzymes).

Result Name	Units	Specifications	Test Value
Absorbance @ 220 nm	A.U.	<= 0.2	0.01
Absorbance @ 230 nm	A.U.	<= 0.1	0.005
Absorbance @ 240 nm	A.U.	<= 0.05	0.003
Absorbance @ 250 nm	A.U.	<= 0.01	0.001
Absorbance @ 260 nm	A.U.	<= 0.005	0
Absorbance @ 270 nm	A.U.	<= 0.005	0.001
Acidity/alkalinity (meq/g)	meq/g	<= 0.0001	0.00003
Assay (GC)	%	>= 99.5	99.99
Chemical form		Mobile liquid	Mobile liquid
Residue after evaporation (ppm)	ppm	<= 2	None Detected
Visual colour		Clear colourless	Clear colourless
Water	%	<= 0.1	0.012
Wavelength @ 1 A.U.	nm	<= 205	202.4

**Additional Information** Filtered to 0.2 micron



Ashok Ganatra  
Supervisor, QC

Products are processed under ISO 9001:2015 quality management systems and samples are tested for conformance to the noted specifications. Certain data may have been supplied by third parties. We disclaim the implied warranties of merchantability and fitness for a particular purpose, and the accuracy of third-party data or information associated with the product. Products are for research use or further manufacturing. Products are not for direct administration to humans or animals. It is the responsibility of the final formulator or end user to determine suitability, and to qualify and/or validate each product for its intended use.

Note: The data listed is valid for all package sizes of this lot of this product, expressed as an extension of the catalogue number listed above.