

## CERTIFICATE OF ANALYSIS

Thermo Fisher Scientific's Quality System has been found to conform to Quality Management System Standard ISO9001:2015 by Intertek. Certificate Number. 2317548

Catalogue Number	13406
Lot Number	A0453396
Description	Potassium hydroxide, ca. 85%, for analysis, pellets
CAS Number	1310-58-3
Quality Test/Release Date	24/Nov/2024
Suggested retest date	24/Nov/2027
Country of Origin	SWEDEN
Declaration of Origin	synthetic

Result Name	Units	Specifications	Test Value
Appearance (Color)		White	White
Appearance (Form)		Pellets	Pellets
Titration with HCl	%	$\geq 85$	88.5
Potassium carbonate	%	$\leq 1$ (K <sub>2</sub> CO <sub>3</sub> )	$\leq 1$ (K <sub>2</sub> CO <sub>3</sub> )
Sodium (Na)	%	$\leq 0.4$	0.29
Chloride (Cl)	ppm	$\leq 70$	21
Silver (Ag)	ppm	$\leq 0.5$	$\leq 0.05$
Aluminium (Al)	ppm	$\leq 10$	$\leq 0.2$
Iron (Fe)	ppm	$\leq 5$	0.5
Nickel (Ni)	ppm	$\leq 3$	$\leq 0.2$
Sulfate (SO <sub>4</sub> )	ppm	$\leq 10$	$\leq 5$
Arsenic (As)	ppm	$\leq 0.5$	$\leq 0.5$
Calcium (Ca)	ppm	$\leq 10$	$\leq 10$
Heavy metals (as Pb)	ppm	$\leq 10$	$\leq 5$
Nitrogen compounds (as N)	ppm	$\leq 5$	$\leq 5$
Phosphate (PO <sub>4</sub> )	ppm	$\leq 4$	$\leq 4$
Silicon dioxide (SiO <sub>2</sub> )	ppm	$\leq 5$	$\leq 5$



Geert Torfs  
Supervisor, QC

Products are processed under ISO 9001:2015 quality management systems and samples are tested for conformance to the noted specifications. Certain data may have been supplied by third parties. We disclaim the implied warranties of merchantability and fitness for a particular purpose, and the accuracy of third-party data or information associated with the product. Products are for research and development use only. Products are not for direct administration to humans or animals. It is the responsibility of the final formulator or end user to determine suitability, and to qualify and/or validate each product for its intended use.

Note: The data listed is valid for all package sizes of this lot of this product, expressed as an extension of the catalogue number listed above.