

## CERTIFICATE OF ANALYSIS

Thermo Fisher Scientific's Quality System has been found to conform to Quality Management System Standard ISO9001:2015 by TUV SUD America Inc.  
 Certificate Number. 951001163

Catalogue Number	011831
Lot Number	M05M009
Description	Ammonium molybdate (para) tetrahydrate, ACS, 81-83% as MoO <sub>3</sub>
CAS Number	12054-85-2
Quality Test/Release Date	05/Jan/2026
Suggested retest date	05/Jan/2031
Country of Origin	United States
Declaration of Origin	Synthetic
BSE/TSE	Not directly derived from or manufactured with any animal byproducts in any way (including but not limited to fermentation or nutrient broth, catalysts, enzymes).

Result Name	Units	Specifications	Test Value
Assay (unspecified)	%	81-83% as MoO <sub>3</sub>	81.4
Heavy Metals	%	(OES-ICP) 0.001%	<0.0010
Impurity content	%	Arsenate, phosphate, and silicate (as SiO <sub>2</sub> ) 0.001%	<0.0010
Impurity content	%	Chloride (as Cl) 0.002%	<0.0020
Impurity content	ppm	K 0.01%	1
Impurity content	ppm	Mg 0.005%	1
Impurity content	ppm	Na 0.01%	1
Impurity content		NO <sub>3</sub> P.T.	Passes Test
Impurity content	ppm	PO <sub>4</sub> 5ppm	<5
Impurity content	%	SO <sub>4</sub> 0.02%	<0.0200
Insoluble material	%	0.005%	<0.0050



Derek Roy  
 Quality Manager, LCD

Products are processed under ISO 9001:2015 quality management systems and samples are tested for conformance to the noted specifications. Certain data may have been supplied by third parties. We disclaim the implied warranties of merchantability and fitness for a particular purpose, and the accuracy of third-party data or information associated with the product. Products are for research and development use only. Products are not for direct administration to humans or animals. It is the responsibility of the final formulator or end user to determine suitability, and to qualify and/or validate each product for its intended use.

Note: The data listed is valid for all package sizes of this lot of this product, expressed as an extension of the catalogue number listed above.