

## CERTIFICATE OF ANALYSIS

Thermo Fisher Scientific's Quality System has been found to conform to Quality Management System Standard ISO9001:2015 by Intertek Global Certificate Number. CERT-0120633

|                           |                                                                                                                         |
|---------------------------|-------------------------------------------------------------------------------------------------------------------------|
| Catalogue Number          | A38                                                                                                                     |
| Lot Number                | 253325                                                                                                                  |
| Description               | ACETIC ACID, GLACIAL, CERTIFIED ACS                                                                                     |
| CAS Number                | 64-19-7                                                                                                                 |
| Quality Test/Release Date | 10/Sep/2025                                                                                                             |
| Suggested retest date     | 09/Sep/2030                                                                                                             |
| Country of Origin         | United States                                                                                                           |
| Declaration of Origin     | Synthetic                                                                                                               |
| BSE/TSE                   | This material is manufactured through a petrochemical synthesis process and is free from ingredients of animal sources. |

| Result Name                    | Units     | Specifications | Test Value              |
|--------------------------------|-----------|----------------|-------------------------|
| APPEARANCE                     |           | REPORT         | Clear, colorless liquid |
| ACETIC ANHYDRIDE               | %         | <= 0.01        | <0.01                   |
| ALUMINUM                       | ppm       | <= 0.3         | <0.3                    |
| ARSENIC AND ANTIMONY           | ppm       | <= 0.005       | <0.005                  |
| ASSAY                          | w/w %     | >= 99.7        | 99.9                    |
| BORON (B)                      | ppm       | <= 0.2         | <0.2                    |
| CALCIUM (Ca)                   | ppm       | <= 0.3         | <0.3                    |
| CHLORIDE                       | ppm       | <= 0.4         | <0.4                    |
| CHROMIUM (Cr)                  | ppm       | <= 0.2         | <0.2                    |
| COLOR                          | APHA      | <= 10          | <10                     |
| COPPER (Cu)                    | ppm       | <= 0.1         | <0.1                    |
| DILUTION TEST                  | PASS/FAIL | = PASS TEST    | PASS TEST               |
| EVAPORATION RESIDUE            | ppm       | <= 8           | <8                      |
| GOLD (Au)                      | ppm       | <= 0.3         | <0.3                    |
| HEAVY METALS (as Pb)           | ppm       | <= 0.5         | <0.5                    |
| IDENTIFICATION                 | PASS/FAIL | = PASS TEST    | PASS TEST               |
| IRON (Fe)                      | ppm       | <= 0.2         | <0.2                    |
| LEAD (Pb)                      | ppm       | <= 0.3         | <0.3                    |
| MAGNESIUM (Mg)                 | ppm       | <= 0.3         | <0.3                    |
| MANGANESE (Mn)                 | ppm       | <= 0.3         | <0.3                    |
| NICKEL (Ni)                    | ppm       | <= 0.1         | <0.1                    |
| PHOSPHATE (PO4)                | ppm       | <= 1           | <1                      |
| POTASSIUM (K)                  | ppm       | <= 0.3         | <0.3                    |
| SODIUM (Na)                    | ppm       | <= 0.3         | <0.3                    |
| SUBSTANCES REDUCING DICHROMATE | PASS/FAIL | = PASS TEST    | PASS TEST               |
| SUBSTANCES REDUCING KMNO4      | PASS/FAIL | = PASS TEST    | PASS TEST               |
| SULFATE (SO4)                  | ppm       | <= 0.4         | <0.4                    |
| TIN (Sn)                       | ppm       | <= 0.3         | <0.3                    |
| TITANIUM (Ti)                  | ppm       | <= 0.3         | <0.3                    |
| TITRATABLE BASE                | MEQ/G     | <= 0.0004      | <0.0004                 |
| ZINC (Zn)                      | ppm       | <= 0.3         | <0.3                    |



Note: The data listed is valid for all package sizes of this lot of this product, expressed as an extension of the catalogue number listed above.

Harout Sahagian  
Manager, QC • Laboratory Products Group

Products are processed under ISO 9001:2015 quality management systems and samples are tested for conformance to the noted specifications. Certain data may have been supplied by third parties. We disclaim the implied warranties of merchantability and fitness for a particular purpose, and the accuracy of third-party data or information associated with the product. Products are for research use or further manufacturing. Products are not for direct administration to humans or animals. It is the responsibility of the final formulator or end user to determine suitability, and to qualify and/or validate each product for its intended use.

Note: The data listed is valid for all package sizes of this lot of this product, expressed as an extension of the catalogue number listed above.