

## CERTIFICATE OF ANALYSIS

Thermo Fisher Scientific's Quality System has been found to conform to Quality Management System Standard ISO9001:2015 by Intertek Global Certificate Number. CERT-0120633

|                           |  |
|---------------------------|--|
| Catalogue Number          | 41121  |
| Lot Number                | B0157261   |
| Description               | HEPARIN SODIUM   |
| CAS Number                | 9041-08-1  |
| Quality Test/Release Date | 20/Jun/2025  |
| Suggested retest date     | 23/Oct/2027  |
| Country of Origin         | United States  |
| Declaration of Origin     | Animal - Porcine   |
| BSE/TSE                   | Derived from porcine intestinal mucosa from healthy pigs that received and passed ante- and post-mortem verification of health by the government veterinarian. The manufacturing process has been validated as being capable of inactivating viruses. TSE has not been found in swine related tissues. |

| Result Name                                   | Units          | Specifications              | Test Value   |
|---|----------------|-----------------------------|--------------|
| APPEARANCE                                    |                | REPORT                      | White powder |
| APPEARANCE OF SOLUTION (5000 IU/ML WATER)     | Clear Solution | IN CLEAR                    | CLEAR        |
| HEAVY METALS (as Pb)                          | ppm            | <= 30                       | <30          |
| IDENTIFICATION                                | PASS/FAIL      | IN PASS TEST                | PASS TEST    |
| INFRARED SPECTRUM                             | PASS/FAIL      | IN PASS TEST                | PASS TEST    |
| LOSS ON DRYING @60 C FOR 4 HOURS              | %              | <= 8                        | 1            |
| NMR (1H-NMR)-OVERSULFATED CHONDROITIN SULFATE | PASS/FAIL      | IN ABSENT                   | ABSENT       |
| NUCLEOTIDE                                    | %              | <= 0.2                      | <0.2         |
| PH OF A 1% SOLUTION                           |                | Inclusive Between 5.5 - 8.0 | 6.5          |
| POTENCY (ASSAY)                               | UNITS/MG       | >= 150                      | 203          |
| PROTEIN                                       | %              | <= 1.0                      | <1.0         |
| RESIDUE AFTER IGNITION                        | %              | Inclusive Between 30 - 43   | 39           |



Harout Sahagian  
QC Manager

Products are processed under ISO 9001:2015 quality management systems and samples are tested for conformance to the noted specifications. Certain data may have been supplied by third parties. We disclaim the implied warranties of merchantability and fitness for a particular purpose, and the accuracy of third-party data or information associated with the product. Products are for research use or further manufacturing. Products are not for direct administration to humans or animals. It is the responsibility of the final formulator or end user to determine suitability, and to qualify and/or validate each product for its intended use.

Note: The data listed is valid for all package sizes of this lot of this product, expressed as an extension of the catalogue number listed above.