

## CERTIFICATE OF ANALYSIS

Thermo Fisher Scientific's Quality System has been found to conform to Quality Management System Standard ISO9001:2015 by INTERTEK SAI Global  
Certificate Number. QMS42099

|                           |                                   |
|---------------------------|-----------------------------------|
| Catalogue Number          | T/0706                            |
| Lot Number                | 2541799                           |
| Description               | Tetrahydrofuran HPLC HPLC         |
| CAS Number                | 109-99-9                          |
| Quality Test/Release Date | 18/Jun/2025                       |
| Expiry Phrase             | Use within 1 year of packing date |
| Country of Origin         | Austria                           |

| Result Name                     | Units | Specifications   | Test Value       |
|---------------------------------|-------|------------------|------------------|
| Absorbance @ 230 nm             | A.U.  | <= 0.5           | 0.155            |
| Absorbance @ 240 nm             | A.U.  | <= 0.26          | 0.094            |
| Absorbance @ 250 nm             | A.U.  | <= 0.1           | 0.074            |
| Absorbance @ 260 nm             | A.U.  | <= 0.05          | 0.038            |
| Absorbance @ 270 nm             | A.U.  | <= 0.04          | 0.004            |
| Absorbance @ 280 nm             | A.U.  | <= 0.02          | 0.002            |
| Acidity                         | meq/g | <= 0.0002        | None Detected    |
| Alkalinity (meq/g)              | meq/g | <= 0.0006        | None Detected    |
| Assay (GC)                      | %     | >= 99.8          | 99.97            |
| Chemical form                   |       | Mobile liquid    | Mobile liquid    |
| Peroxide                        | %     | <= 0.0075        | 0.0024           |
| Residue after evaporation (ppm) | ppm   | <= 2             | None Detected    |
| Visual colour                   |       | Clear colourless | Clear colourless |
| Water                           | %     | <= 0.03          | 0.004            |
| Wavelength @ 1 A.U.             | nm    | <= 215           | 211.2            |

**Additional Information** Filtered to 0.2 micron. 'Not suitable for concentration or distillation. Check peroxide level periodically and if >100 ppm DO NOT USE'



Ashok Ganatra  
Supervisor, QC

Products are processed under ISO 9001:2015 quality management systems and samples are tested for conformance to the noted specifications. Certain data may have been supplied by third parties. We disclaim the implied warranties of merchantability and fitness for a particular purpose, and the accuracy of third-party data or information associated with the product. Products are for research use or further manufacturing. Products are not for direct administration to humans or animals. It is the responsibility of the final formulator or end user to determine suitability, and to qualify and/or validate each product for its intended use.

Note: The data listed is valid for all package sizes of this lot of this product, expressed as an extension of the catalogue number listed above.