

CERTIFICATE OF ANALYSIS

Thermo Fisher Scientific's Quality System has been found to conform to Quality Management System Standard ISO9001:2015 by TUV SUD America Inc.
 Certificate Number. 951001163

Catalogue Number	014028
Lot Number	N06M005
Description	Barium zirconium oxide, 99% (metals basis)
CAS Number	12009-21-1
Quality Test/Release Date	06/Feb/2026
Suggested retest date	06/Feb/2036
Country of Origin	United States

Result Name	Units	Specifications	Test Value
Assay (special)	%	(Ba+Sr)O: 54.0-55.0%	54.50
Assay (special)	%	Acetic Acid Soluble Ba: ≤3.0%	1.4
Assay (special)	%	Al ₂ O ₃ : Report	0.0
Assay (special)	%	CaO: Report	0.07
Assay (special)	%	Fe ₂ O ₃ : Report	0.02
Assay (special)	%	MgO: Report	0.0
Assay (special)	%	Na ₂ O: Report	0.0080
Assay (special)	%	SiO ₂ : Report	0.0180
Assay (special)	%	SrO: Report	0.4100
Assay (special)	%	TiO ₂ : Report	0.0440
Assay (special)	%	ZrO ₂ + HfO ₂ : 44.0-45.0%	45
Form		Powder	Powder
Loss on ignition	%	≤1.0%	0.24
Total Metal Impurities	%	≤1.0% (totalled from Al ₂ O ₃ , CaO, Fe ₂ O ₃ , MgO, Na ₂ O, SiO ₂ , SrO, TiO ₂)	0.57
Particle Size	%	+325 Mesh Screen: ≤0.02%	0.00
Particle Size	micron	Horiba LA-950 D50: 1.0-2.0 micron	1.5



Derek Roy
 Quality Manager, LCD

Products are processed under ISO 9001:2015 quality management systems and samples are tested for conformance to the noted specifications. Certain data may have been supplied by third parties. We disclaim the implied warranties of merchantability and fitness for a particular purpose, and the accuracy of third-party data or information associated with the product. Products are for research and development use only. Products are not for direct administration to humans or animals. It is the responsibility of the final formulator or end user to determine suitability, and to qualify and/or validate each product for its intended use.

Note: The data listed is valid for all package sizes of this lot of this product, expressed as an extension of the catalogue number listed above.