

CERTIFICATE OF ANALYSIS

Thermo Fisher Scientific's Quality System has been found to conform to Quality Management System Standard ISO9001:2015 by INTERTEK SAI Global
Certificate Number. QMS42099

Catalogue Number 38950
Lot Number 2664447
Description Isopropyl acetate AR For analysis
CAS Number 108-21-4
Quality Test/Release Date 21/Jan/2026
Expiry Phrase Use within 3 yrs of opening
Country of Origin United States of America

Result Name	Units	Specifications	Test Value
Acidity (as CH ₃ COOH)	%	<= 0.01	0.0012
Assay (GC)	%	>= 99	99.91
Cadmium (Cd)	ppm	<= 0.05	<0.005
Calcium (Ca)	ppm	<= 0.5	<0.02
Chemical form		Mobile liquid	Mobile liquid
Chromium (Cr)	ppm	<= 0.02	<0.01
Cobalt (Co)	ppm	<= 0.02	<0.005
Colour	APHA	<= 10	<5
Copper (Cu)	ppm	<= 0.02	<0.01
IR		Must be 'Pass'	Pass
Iron (Fe)	ppm	<= 0.1	<0.05
Lead (Pb)	ppm	<= 0.1	<0.005
Magnesium (Mg)	ppm	<= 0.1	<0.01
Manganese (Mn)	ppm	<= 0.02	<0.005
Nickel (Ni)	ppm	<= 0.02	<0.005
Propan-2-ol	%	<= 0.1	0.0026
Refractive index		>= 1.376 and <= 1.378	1.3773
Residue after evaporation (%)	%	<= 0.002	None Detected
Visual colour		Clear colourless	Clear colourless
Water	%	<= 0.1	0.019
Zinc (Zn)	ppm	<= 0.1	<0.02

A. Ganatra

Ashok Ganatra
Supervisor, QC

Products are processed under ISO 9001:2015 quality management systems and samples are tested for conformance to the noted specifications. Certain data may have been supplied by third parties. We disclaim the implied warranties of merchantability and fitness for a particular purpose, and the accuracy of third-party data or information associated with the product. Products are for research use or further manufacturing. Products are not for direct administration to humans or animals. It is the responsibility of the final formulator or end user to determine suitability, and to qualify and/or validate each product for its intended use.

Note: The data listed is valid for all package sizes of this lot of this product, expressed as an extension of the catalogue number listed above.