



CERTIFICATE OF COMPLIANCE

ProAmpac Job No.:S14993

Part Description: SealPAK 502-24 165MM X 203MM

Raw Material Description: 4.5 mil High Barrier Clear Polyester

12 μ PET/100 LLDPE (Sealant)

Method of Testing: CONWI-44 Burst Test Procedure

Burst Results (For Reference Only) (psi): Average: 8.50 Minimum: 7.07 Specification: 6.00 min

Gauge (mil): Minimum: 4.50 Maximum: 4.50

Average: 4.50 Specification: 4.5 mil ($\pm 10\%$)

We certify that the articles furnished above are in compliance with the applicable drawings, specifications, terms and provisions of the purchase agreement and meets all product specifications.

Representative:

Kirk Gambrell
Laboratory Technician

Date: 1/9/2024